



EH010

Daily time switch 1 channel, 16A, 1 module

Technical characteristics

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Switch mode	NO contact
-------------	------------

Main electrical features

Frequency	50 Hz
-----------	-------

Dimensions

Depth of installed product	60 mm
Height of installed product	80 mm
Width of installed product	18 mm

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Power dissipation per coil	0.5 W

Incandescent bulbs control

Max. power with incandescent lamps	900 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

Settings

Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Programming cycle	24H
Setting	Setting via day dial

Equipment

Number of channels	1
Supply failure reserve	without

Use

Cycle	daily
-------	-------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...55 °C
Working accuracy	1