




EN145



Interface relay VLV/ LV

Technical characteristics

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	2 W
---------------------------	-----

Connection

Connection cross-sect. flexible conductor	0,5 / 4mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------