




EN145



## Interface relay VLV/ LV

### Technical Characteristics

Rated operational voltage Ue	250 V
Frequency	50/60 Hz
Rated current	5 A
Rated insulation voltage	250 V
Acceptable current rating with AC1	5 A
Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm
Total power loss under IN	2 W
Number of modules	1
Connection cross-sect. flexible conductor	0,5 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
Type of connection	with screw
Number of contacts	1
Type of contacts	1 changeover
Can be accessorized	No
European directive WEEE	concerned
Operating temperature	-10...50 °C