




EN146



Interface relay LV / VLV

Technical characteristics

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	2 W
---------------------------	-----

Connection

Number of contacts	1
Type of contacts	1 changeover

Standards

European directive WEEE	concerned
-------------------------	-----------

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------