



Auxiliary contact 1NC+1NO

Technical characteristics

Electric current

Rated current	2 A
---------------	-----

Voltage

Rated insulation voltage U_i	250 V
--------------------------------	-------

Capacity

Number of modules	0.50
-------------------	------

Use conditions

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²
Type of contacts	1NC+1NO

Power

Total power loss under IN	0.10 W
---------------------------	--------

Dimensions

Height	83 mm
Width	8.75 mm
Depth	58 mm