




EPN051



Auxiliary contact 1NC+1NO

Technical characteristics

Main electrical features

| | |
|------------------------------|-------|
| Rated operational voltage Ue | 250 V |
|------------------------------|-------|

Voltage

| | |
|--------------------------|-------|
| Rated insulation voltage | 250 V |
|--------------------------|-------|

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 58 mm |
| Height of installed product | 83 mm |
| Width of installed product | 8.75 mm |

Power

| | |
|---------------------------|-------|
| Total power loss under IN | 0.1 W |
|---------------------------|-------|

Connection

| | |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm ² |
| Connection cross-sect. rigid cable | 1,5 / 10mm ² |
| Number of contacts | 2 |
| Type of contacts | 1NC+1NO |

Standards

| | |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...40 °C |
|-----------------------|------------|