



EPN540



## Latching relay 4NO 230V

### Technical characteristics

#### Main electrical features

Rated operational voltage $U_e$	250 / 400 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	400 V
--------------------------	-------

#### Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	35 mm

#### Power

Total power loss under IN	4.8 W
---------------------------	-------

#### Endurance

Number of mechanical operations	500000
---------------------------------	--------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

#### Incandescent bulbs control

Max. power with incandescent lamps	1800 W
------------------------------------	--------

#### Installation, mounting

Tightening torque	1,6Nm
-------------------	-------

#### Connection

Type of connection	with screw
Number of contacts	4

#### Standards

Standard text	IEC/EN 60669-2
---------------	----------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------