



ERC225

**Override Contactor 25A, 2NO, 230V~50Hz**

**Technical characteristics**

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	250 V
Rated impulse withstand voltage	4 kV

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

**Power**

Total power loss under IN	4 W
Power dissipation per coil	1 W

**Endurance**

Electric endurance in number of cycles	30000
Number of mechanical operations	100000

**Fluorescent bulbs control**

Max. power with fluorescent parallel lamps	810 VA
--	--------

**Incandescent bulbs control**

Max. power with incandescent lamps	1900 W
------------------------------------	--------

**Equipment**

Can be accessorized	Yes
---------------------	-----

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP2X
---------------------	------

**Use conditions**

Operating temperature	-10...50 °C
-----------------------	-------------