



ESC080

Auxiliary contact 6A, 1NO+1NC

Technical characteristics

Main electrical features

Rated operational voltage Ue 230 V

Voltage

Rated insulation voltage 240 V

Rated impulse withstand voltage 4 kV

Electric current

Acceptable current rating with AC1 6 A

Dimensions

Depth of installed product 60 mm

Height of installed product 83 mm

Width of installed product 11 mm

Power

Total power loss under IN 0.1 W

Endurance

Electric endurance in number of cycles 30000

Number of mechanical operations 1000000

Connection

Number of contacts 2

Standards

European directive WEEE concerned

Safety

Protection class isol.class II

Use conditions

Operating temperature -10...50 °C