



ESC340S

Humfree Contactor 40A, 3NO, 230V~50/60Hz

Technical characteristics

Architecture

Number of poles 3 P

Main electrical features

Rated operational voltage U_e 400 V

Frequency 50 Hz

Voltage

Rated insulation voltage 440 V

Rated impulse withstand voltage 4 kV

Dimensions

Depth of installed product 60 mm

Height of installed product 85 mm

Width of installed product 54 mm

Power

Total power loss under IN 14.1 W

Power dissipation per coil 4.5 W

Endurance

Electric endurance in number of cycles 30000

Number of mechanical operations 1000000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps 1300 VA

Incandescent bulbs control

Max. power with incandescent lamps 4000 W

Connection

Number of contacts 3

Equipment

Can be accessorized Yes

Standards

European directive WEEE concerned

Safety

Protection index IP IP2X

Protection class isol.class II

Use conditions

Operating temperature

-10...50 °C