



ESC464

## Contacteur 63A, 4NC, 230V~50Hz

### Technical characteristics

#### Architecture

Number of poles	4 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

#### Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Width of installed product	54 mm

#### Power

Total power loss under IN	20 W
Power dissipation per coil	1.5 W

#### Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	2100 VA
--	---------

#### Incandescent bulbs control

Max. power with incandescent lamps	6500 W
------------------------------------	--------

#### Connection

Number of contacts	4
--------------------	---

#### Equipment

Can be accessorized	Yes
---------------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP2X
Protection class	isol.class II

**Use conditions**

---

Operating temperature

-10...50 °C