



ETC425

Night & Day Contactor 25A, 4NO, 230V~50Hz

Technical characteristics

Architecture

Number of poles	4 P
-----------------	-----

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50 Hz

Voltage

Rated insulation voltage	440 V
Rated impulse withstand voltage	4 kV

Dimensions

Depth of installed product	64 mm
Height of installed product	83 mm
Width of installed product	35.75 mm

Power

Total power loss under IN	7.5 W
Power dissipation per coil	1.5 W

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	100000

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	810 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	1900 W
------------------------------------	--------

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 10mm ²
Type of connection	with screw
Number of contacts	4
Type of contacts	4NO

Equipment

Can be accessorized

Yes

Safety

Protection class

isol.class II

Use conditions

Operating temperature

-10...50 °C