



ETC440

## Night & Day Contactor 40A, 4NO, 230V~50Hz

### Technical characteristics

#### Architecture

Number of poles	4 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	400 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	440 V
--------------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	54 mm
----------------------------	-------

#### Power

Total power loss under IN	14.3 W
---------------------------	--------

Power dissipation per coil	1.5 W
----------------------------	-------

#### Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations	1000000
---------------------------------	---------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	1300 VA
--	---------

#### Incandescent bulbs control

Max. power with incandescent lamps	4000 W
------------------------------------	--------

#### Connection

Number of contacts	4
--------------------	---

#### Equipment

Can be accessorized	Yes
---------------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP2X
---------------------	------

Protection class	isol.class II
------------------	---------------

**Use conditions**

---

Operating temperature

-10...50 °C