



EV102



Universal remote control dimmer 1000W + display

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Depth of installed product	65 mm
Height of installed product	85 mm
Width of installed product	88.5 mm

Power

Halogen switching capacity 230V	20 / 1000 W
Power consumed	6 W
Power consumption (operation)	15 W
Incandescent bulb power	20 / 1000 W
Total power loss under IN	1 W
Power dissipation per coil	1.3 W

Materials

Surface appearance	matt
--------------------	------

Incandescent bulbs control

Max. power with incandescent lamps	1000 W
------------------------------------	--------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 16mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of load	universal

Settings

Setting	Brightness limit and dimming speed adjustable via display
---------	---

Equipment

Dimming principle	automatic load detection
-------------------	--------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

