




EVN002



IP20

Remote Control Dimmer universal 500W

Technical characteristics

Architecture

Fixing mode Din-Rail

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Fuse

Fuse with electronic short-circuit and overload protection

Dimensions

Depth of installed product 62 mm

Height of installed product 85 mm

Width of installed product 35 mm

Power

Halogen switching capacity 230V 500 W

Power consumed 4.5 W

Power consumption (operation) 4.5 W

Incandescent bulb power 500 W

Total power loss under IN 0.2 W

Materials

RAL colour RAL 9001 - Cream

Surface appearance matt

Incandescent bulbs control

Max. power with incandescent lamps 500 W

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 1,5 / 6mm²

Connection cross-sect. rigid cable 1,5 / 6mm²

Type of load universal

Type of connection with screw

Type of connection with screw terminals

Equipment

Dimming principle automatic load detection

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-20...50 °C