




EVN004



IP20

Remote Control Dimmer universal 500W

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Fuse

Fuse	with electronic short-circuit and overload protection
------	---

Dimensions

Depth of installed product	62 mm
Height of installed product	85 mm
Width of installed product	35 mm

Power

Halogen switching capacity 230V	500 W
Power consumed	4.5 W
Power consumption (operation)	4.5 W
Incandescent bulb power	500 W
Total power loss under IN	0.2 W

Materials

Surface appearance	matt
--------------------	------

Incandescent bulbs control

Max. power with incandescent lamps	500 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Type of load	universal

Settings

Setting	setting of comfort functions (1...4) via adjusting wheel ; Reset of settings for special functions
---------	--

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-20...50 °C
-----------------------	-------------