



EVN011



IP20

Remote Control Dimmer universal 300W

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Fuse

Fuse	with electronic short-circuit and overload protection
------	---

Dimensions

Depth of installed product	65 mm
Height of installed product	90 mm
Width of installed product	17.5 mm

Power

Halogen switching capacity 230V	300 W
Power consumed	2.1 W
Power consumption (operation)	2.1 W
Incandescent bulb power	300 W
Total power loss under IN	0.2 W

Materials

Surface appearance	matt
--------------------	------

Incandescent bulbs control

Max. power with incandescent lamps	300 W
------------------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1,5 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 6mm ²
Type of load	universal
Type of connection	with screw
Type of connection	with screw terminals

Equipment

Dimming principle	automatic load detection
-------------------	--------------------------

Use conditions

Operating temperature	-10...45 °C
-----------------------	-------------