



EVN012



IP20

## Universal Remote Control Dimmers 300W Comfort

### Technical characteristics

#### Architecture

Fixing mode Din-Rail

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Fuse

Fuse with electronic short-circuit and overload protection

#### Dimensions

Depth of installed product 65 mm

Height of installed product 90 mm

Width of installed product 17.5 mm

#### Power

Halogen switching capacity 230V 300 W

Power consumed 2.1 W

Power consumption (operation) 2.1 W

Incandescent bulb power 300 W

Total power loss under IN 0.2 W

#### Materials

RAL colour RAL 9001 - Cream

Surface appearance matt

#### Incandescent bulbs control

Max. power with incandescent lamps 300 W

#### Installation, mounting

Mounting type din-Rail

#### Connection

Connection cross-sect. flexible conductor 1,5 / 6mm<sup>2</sup>

Connection cross-sect. rigid cable 1,5 / 6mm<sup>2</sup>

Type of load universal

Type of connection with screw

Type of connection with screw terminals

#### Equipment

Dimming principle automatic load detection

**Safety**

---

Protection index IP

IP20

**Use conditions**

---

Operating temperature

-10...45 °C