



FL167A

Steel enclosure, Orion.Plus, glazed door 650x400x200 mm

Technical characteristics

Dimensions

Depth of installed product	200 mm
Height of installed product	650 mm
Width of installed product	400 mm

Cover, door

Type of door closing	lock with male triangular wrench
Interlockable	Yes

Materials

Colour	RAL 7035
Type of surface treatment	powder-coated

Equipment

Number of rows	4
Quantity of section in width	0

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
------------------	--------------