

125 A



## Polyester enclosure, Orion.Plus, plain door 350x300x160 mm

## **Technical characteristics**

Dimensions	
Height	350 mm
Width	300 mm
Depth	160 mm
Thickness of sidewall	2 mm
Safety	
Ingress Protection (IP) class	IP66
Protection class	Isolation class II
Locking type	3-Side 7 mm, Key lock
Impact resistance IK	IK10
Equipment	
Number of flange plate openings	0
Number of rows	2
Installation, mounting	
Mounting on	Surface mounting
Suitable for outdoor usage	Yes
Materials	
Colour	Light grey
RAL code	7035
Treatment	Untreated
Material	Glass reinforced polyester
Cover, door	
Number of cabinet doors	1
Number of locks	2
Door/cover is transparent	No
Electric current	

Rated current