



FL266B

**Polyester enclosure, Orion.Plus, glazed door 650x400x200 mm**

**Technical Characteristics**

Fixing mode	Wall mounting
Rated current	630 A
Depth of installed product	200 mm
Height of installed product	650 mm
Width of installed product	400 mm
Number of modules	72
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	glas reeinforced polyester
Type of surface treatment	untreated
Number of rows	4
Can be accessorized	No
European directive WEEE	not concerned
Protection index IP	IP66
Protection class	isol.class II