



FL327B

Polyester floor standing enclosure, Orion.Plus, plain door 1200x850x300 mm

Technical characteristics

Architecture

Fixing mode Wall mounting

Dimensions

Depth of installed product 300 mm

Height of installed product 1200 mm

Width of installed product 850 mm

Cover, door

Type of door closing Barrel lock

Interlockable Yes

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material glas reeinforced polyester

Type of surface treatment powder-coated

Equipment

Number of rows 7

Quantity of section in width 1

Standards

European directive WEEE concerned

Safety

Protection index IP IP65

Protection class isol.class II