



FWB73

FWB encl.,univers,7rows 252 mod cl.II IP44,plain door,1100x800x161mm,brass term.

Technical characteristics

Connection

Number of conduit inlets	12
--------------------------	----

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	125 A
---------------	-------

Equipment

Number of rails	21
Number of rows	7
Number of section in width	3
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

Capacity

Number of modules	252
-------------------	-----

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	1,100 mm
Width	800 mm
Depth	165 mm
Built-in depth	161 mm
Number of width units	36

Cover, door

Number of cabinet doors	2
Number of locks	0
Type of handle	Hinged pattern handle
Door/cover is transparent	No

Connectivity

Mounting type	Surface mounting
---------------	------------------

Subject to technical modifications

Materials

Material	Steel
RAL code	9010
Colour	Pure white

Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Bar lock, Without lock