



FWB74S

**FWB encl.,univers,7-rows 336 modules cl.II IP44 w.plain door, 1100x1050x161mm,QC**

**Technical characteristics**

**Connection**

Number of conduit inlets	16
--------------------------	----

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	125 A
---------------	-------

**Equipment**

Number of rails	28
Number of rows	7
Number of section in width	4
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

**Capacity**

Number of modules	336
-------------------	-----

**Functions**

Has protection main switch	No
With conduit inlets	Yes

**Dimensions**

Height	1,100 mm
Width	1,050 mm
Depth	165 mm
Built-in depth	0.00 mm
Number of width units	48

**Cover, door**

Number of cabinet doors	2
Number of locks	1
Type of handle	Hinged pattern handle
Door/cover is transparent	No

**Connectivity**

Mounting type	Surface mounting
---------------	------------------

**Materials**

---

Material	Steel
RAL code	9010
Colour	Pure white

---

**Safety**

---

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP44
Locking type	Bar lock, Without lock
Glow wire test	750 °C

---