



GD102E

Mini-enclosure, gamma, 2 module, protect. class IP30

Technical characteristics

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	32 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No
Has earthing terminal block	No
Has mounting plate	No

Capacity

Number of modules	2
-------------------	---

Functions

Has protection main switch	No
With conduit inlets	Yes

Dimensions

Height	160 mm
Width	55 mm
Depth	82 mm
Number of width units	2

Cover, door

Number of locks	0
Door/cover is transparent	No

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Plastic
----------	---------

RAL code	9010
Colour	Pure white
Safety	
Protection class	Isolation class II
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C