



GD24H

## Technical characteristics

### Architecture

Fixing mode	surface-mounting
-------------	------------------

### Main electrical features

Rated operational voltage Ue	216 / 230 / 253 V
Frequency	50 Hz

### Dimensions

Depth of installed product	113 mm
Height of installed product	193 mm
Width of installed product	168 mm

### Cover, door

Type of door closing	Barrel lock
Interlockable	No

### Materials

Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white

### Equipment

Number of rows	1
Can be accessorized	No