



GD24H

2 Way Garage CU 40A 30mA RCCB, 1*32A, 1*6A MCB IP30

Technical Characteristics

Fixing mode	surface-mounting
Rated operational voltage Ue	216 / 230 / 253 V
Frequency	50 Hz
Rated current	40 A
Depth of installed product	113 mm
Height of installed product	193 mm
Width of installed product	168 mm
Number of modules	4
Type of door closing	Barrel lock
Interlockable	No
Colour	white
Colour	white
RAL colour	RAL 9010 - Pure white
RAL colour number	9010
Material	Polycarbonate (PC)
Number of rows	1
Can be accessorized	No
Protection index IP	IP30