



HA358

## Load break switch 3P 630A

### Technical characteristics

#### Architecture

Number of poles	3 P
Type of pole	3 P

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

#### Voltage

Rated insulation voltage	1000 V
Rated impulse withstand voltage	8000 V

#### Dimensions

Depth of installed product	165 mm
Height of installed product	260 mm
Width of installed product	230 mm

#### Power

Total power loss under IN	92.7 W
---------------------------	--------

#### Cover, door

Interlockable	Yes
---------------	-----

#### Connection

Connection cross-sect. flexible conductor	185mm <sup>2</sup>
Connection cross-sect. rigid cable	2x300mm <sup>2</sup>

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

#### Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------