



HAC406

## Load break switch 4P 63A

### Technical characteristics

#### Architecture

Number of poles	4 P
-----------------	-----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

#### Power

Total power loss under IN	6 W
---------------------------	-----

#### Cover, door

Interlockable	Yes
---------------	-----

#### Installation, mounting

Tightening torque	3.5 - 3.85 Nm
-------------------	---------------

#### Connection

Type of connection	with screw
--------------------	------------

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------