



HAC410

Load break switch 4P 100A

Technical Characteristics

Number of poles	4 P
Type of pole	4 P
Rated operational voltage Ue	380 / 415 V
Frequency	50 Hz
Rated current	100 A
Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V
Total power loss under IN	16 W
Number of modules	4
Interlockable	Yes
Connection cross-sect. rigid cable	35mm ²
Type of connection	with screw
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20
Operating temperature	-20...70 °C