



HBA125H

Electronic earth leakage add-on block 3P 125A I_{dn} adjustable, time

Technical characteristics

Architecture

Neutral position	not applicable
Number of poles	3 P

Main electrical features

Rated operational voltage U _e	220 / 415 V
--	-------------

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
----------------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Residual current type	A HI
-----------------------	------