



HBA127H

Electronic earth leakage add-on block 3P 125A Sensitivity fix

Technical Characteristics

Neutral position	not applicable
Number of poles	3 P
Fixing mode	DIN rail type O (symmetrical)
Rated operational voltage Ue	220 / 415 V
Rated current	125 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV
Rated residual operating current	300 mA
European directive WEEE	concerned
Protection index IP	IP4X
Residual current type	A HI