



HBA128H

Electronic earth leakage add-on block 4P 125A Sensitivity fix

Technical characteristics

Architecture

Neutral position	not applicable
Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	220 / 415 V
------------------------------	-------------

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	300 mA
----------------------------------	--------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
Residual current type	A HI