



HBA160H

Electronic earth leakage add-on block 3P 160A I_{dn} adjustable, time delay

Technical characteristics

Architecture

Number of poles 3 P

Fixing mode DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage U_e 220 / 415 V

Voltage

Rated insulation voltage 500 V

Rated impulse withstand voltage 6 kV

Electric current

Rated residual operating current 30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A

Standards

European directive WEEE concerned

Safety

Residual current type A HI