



HBA160H

## Electronic earth leakage add-on block 3P 160A I<sub>dn</sub> adjustable, time delay

### Technical characteristics

#### Architecture

Neutral position	not applicable
Number of poles	3 P

#### Main electrical features

Rated operational voltage U <sub>e</sub>	220 / 415 V
--	-------------

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

#### Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
----------------------------------	---

#### Safety

Residual current type	A HI
-----------------------	------