



HBA161H

Electronic earth leakage add-on block 4P 160A I_{dn} adjustable, time delay

Technical characteristics

Architecture

| | |
|------------------|----------------|
| Neutral position | not applicable |
| Number of poles | 4 P |

Main electrical features

| | |
|--|-------------|
| Rated operational voltage U _e | 220 / 415 V |
|--|-------------|

Voltage

| | |
|---------------------------------|-------|
| Rated insulation voltage | 500 V |
| Rated impulse withstand voltage | 6 kV |

Electric current

| | |
|----------------------------------|---|
| Rated residual operating current | 30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A |
|----------------------------------|---|

Safety

| | |
|-----------------------|------|
| Residual current type | A HI |
|-----------------------|------|