



HBB161H

**Electronic earth leakage add-on block 4P 160A I<sub>dn</sub> adjustable, time delay**

**Technical Characteristics**

Neutral position	not applicable
Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)
Rated operational voltage U <sub>e</sub>	220 / 415 V
Rated current	160 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV
Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
European directive WEEE	concerned
Protection index IP	IP4X
Residual current type	A HI