



HBB251H

Electronic earth leakage add-on block 4P 250A I_{dn} adjustable, time

Technical characteristics

Architecture

Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage U _e	220 / 415 V
--	-------------

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
----------------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
Residual current type	A HI