



HBB251H

Electronic earth leakage add-on block 4P 250A I_{dn} adjustable, time delay

Technical Characteristics

Neutral position	not applicable
Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)
Rated operational voltage U _e	220 / 415 V
Rated current	250 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV
Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
European directive WEEE	concerned
Protection index IP	IP4X
Residual current type	A HI