



HBD401H

## Electronic earth leakage add-on block 4P 400A I<sub>dn</sub> adjustable, time delay

### Technical characteristics

#### Architecture

Number of poles 4 P

#### Main electrical features

Rated operational voltage U<sub>e</sub> 220 / 415 V

Frequency 50/60 Hz

#### Voltage

Rated insulation voltage 500 V

Rated impulse withstand voltage 6000 V

#### Electric current

Rated residual operating current 30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A

#### Power

Total power loss under I<sub>N</sub> 24 W

#### Connection

Connection cross-sect. rigid cable 240 mm<sup>2</sup>

#### Standards

Standard text IEC 60947-2

European directive WEEE concerned

#### Safety

Residual current type A