



HBD401H

Electronic earth leakage add-on block 4P 400A I_{dn} adjustable, time delay

Technical characteristics

Architecture

Number of poles	4 P
-----------------	-----

Main electrical features

Rated operational voltage U _e	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
----------------------------------	---

Power

Total power loss under I _N	24 W
---------------------------------------	------

Connection

Connection cross-sect. rigid cable	240 mm ²
------------------------------------	---------------------

Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

Safety

Residual current type	A
-----------------------	---