



HBT160H

**RCD add on P250 4P 160A Idn adj**

**Technical characteristics**

**Electric current**

Rated current	160 A
Rated residual operating current $I_{\Delta n}$	30 mA, 100 mA, 300 mA, 1000 mA, 3000 mA, 6000 mA

**Architecture**

Number of poles	4
-----------------	---

**Safety**

Residual current type	A
-----------------------	---

**Voltage**

Rated insulation voltage $U_i$	500 V
Rated impulse withstand voltage $U_{imp}$	6,000 V

**Connection**

Cross-section of input and output with screws, for massive conductors	35 - 185 mm <sup>2</sup>
Cross-section of input and output with screws, for flexible conductors	35 - 150 mm <sup>2</sup>