



HBT160L

Alarm add on P250 4P 160A I_{dn} adj

Technical characteristics

Architecture

Neutral position	left
Number of poles	4 P
Fixing mode	fixing plate

Main electrical features

Rated operational voltage U _e	220 / 415 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
----------------------------------	---

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
Residual current type	A