



HBT250H

RCD add on P250 4P 250A Idn adj

Technical characteristics

Electric current

Rated current	250 A
Rated residual operating current Idn	30 mA, 100 mA, 300 mA, 1000 mA, 3000 mA, 6000 mA

Architecture

Number of poles	4
-----------------	---

Safety

Residual current type	A HI
-----------------------	------

Voltage

Rated insulation voltage Ui	500 V
Rated impulse withstand voltage Uimp	6,000 V

Connection

Cross-section of input and output with screws, for massive conductors	35 - 185 mm²
Cross-section of input and output with screws, for flexible conductors	35 - 150 mm²