



HBT250L

**Alarm add on P250 4P 250A I<sub>dn</sub> adj**

**Technical characteristics**

**Architecture**

Neutral position	left
Number of poles	4 P
Fixing mode	fixing plate

**Main electrical features**

Rated operational voltage U <sub>e</sub>	220 / 415 V
Type of supply voltage	AC

**Voltage**

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

**Electric current**

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
----------------------------------	-------------------------------------------

**Standards**

European directive WEEE	concerned
-------------------------	-----------

**Safety**

Protection index IP	IP4X
Residual current type	A