



HBW630H

RCD add on P630 4P 630A I_{dn} adj

Technical characteristics

Architecture

Neutral position	left
Number of poles	4 P

Main electrical features

Rated operational voltage U _e	220 / 415 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	100 mA / 300 mA / 500 mA / 1 A / 3 A / 10 A
----------------------------------	---

Safety

Residual current type	A
-----------------------	---