

HCB251Z

Switch X250 4P 250A

Technical characteristics

Electric current

Rated current	250 A
---------------	-------

Rated short-time withstand current I _{cw} IEC 60947	3 kA
--	------

Architecture

Number of poles	4
-----------------	---

Control/operation element	Toggle
---------------------------	--------

Connection

Cross-section rigid conductor	35 - 185 mm ²
-------------------------------	--------------------------

Cross-section flexible conductor	35 - 150 mm ²
----------------------------------	--------------------------

Voltage

Rated insulation voltage U _i	800 V
---	-------

Rated impulse withstand voltage U _{imp}	8,000 V
--	---------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Functions

Trip unit	Switch
-----------	--------