



HCD400H

## Switch h630 3P 400A

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Power

Total power loss under IN	62.4 W
---------------------------	--------

#### Endurance

Electric endurance in number of cycles	4500
Number of mechanical operations	15000

#### Cover, door

Interlockable	Yes
---------------	-----

#### Connection

Connection cross-sect. flexible conductor	35 / 240mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 240mm <sup>2</sup>

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0

#### Standards

Standard text	IEC 60947-3
European directive WEEE	concerned

#### Use conditions

Operating temperature	-25...70 °C
-----------------------	-------------