



HHA025U

Moulded Case Circuit Breaker h3 x160 TM ADJ 3P3D 25A 25kA CTC

Technical characteristics

Architecture

Neutral position	without neutral
Number of poles	3 P
Type of pole	3P3D

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

Electric current

Rated service breaking capacity Ics under 400V AC according IEC 60947-2	20 kA
---	-------

Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm

Power

Total power loss under IN	13.7 W
---------------------------	--------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Connection

Type of connection	with screw
--------------------	------------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

Standards

Standard text	IEC 60947-2
---------------	-------------