



HHA030E

## Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 32A 25kA CTC

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of poles	1 P
Type of pole	1P1D

#### Main electrical features

Rated operational voltage Ue	220 / 240 V
Frequency	50/60 Hz
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV

#### Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	25 mm

#### Power

Total power loss under IN	2.81 W
---------------------------	--------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Installation, mounting

Tightening torque	6Nm
-------------------	-----

#### Connection

Connection cross-sect. flexible conductor	6 / 70mm <sup>2</sup>
Connection cross-sect. rigid cable	6 / 95mm <sup>2</sup>

#### Cable

Cable Material	Cu
----------------	----

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes
<b>Standards</b>	
Standard text	IEC 60947-2
European directive WEEE	concerned